

# **Master Strain Gage Application Kit**

# **FEATURES**

- Includes supplies and special tools for making a wide range of strain gage installations for both laboratory and field applications.
- · Successfully complete any organic strain gage installation for operation from -452° to +500°F (-269° to
- All materials, including complete instructions, conveniently packaged in a molded, crush-proof, copolymer toolbox. CSM Degreaser, previously supplied in this kit, is to be ordered separately, as needed.
- All application kits should be stored at or near +75°F (+24°C). Refer to product label for most recent information.



## **KIT CONTENTS**

#### **Surface Preparation Materials:**

MCA-1, M-Prep Conditioner A, 1 bottle MN5A-1, M-Prep Neutralizer 5A, 1 bottle Silicon-Carbide Paper: 220, 320, 400 grit,

one 10-ft (3-m) roll each CSP-1, Cotton Swab, 4 packages

GSP-1, Gauze Sponges, 2 packages

RSK-1, Rosin Solvent, two 1-oz (30-ml) bottles

## **Application Tools:**

SSH-1, Surgical Shears

SSC-1, Surgical Scalpel and Blade

SSC-2, Scalpel Blades (5)

BTW-1. Tweezers

STW-1, Tweezers

DP-1, 4-H Drafting Pencil

DWC-1, Diagonal Cutters

DPR-1, Dental Probe (2)

NNP-1, Needle-Nosed Pliers

SSS-1. Steel Scale

SPT-1, Spatula

SPT-2, Spatula

### Hardware:

PCT-3MD Gage Installation Tape

PDT-3, Drafting Tape, 2 dispenser rolls

MJG-2, Mylar® Tape, 1 roll

HSC-1, No. 1 Spring Clamps (4)

HSC-2, No. 2 Spring Clamps (2)

HSC-3, No. 3 Spring Clamp (1)

TFE-1, Teflon® Film, 1 roll

GT-14, Pressure Pads and Plates Kit

#### Adhesives:

M-Bond 200. 1 kit M-Bond AE-10, 1 kit M-Bond 610, 1 kit

### **Soldering Supplies:**

361A-20R, 1 lb (0.45 kg) 361A-20R-25, 1 roll 450-20S-25, 1 roll 570-28R-20, 1 roll FAR-2 M-Flux AR, 1 kit CPF-AST, Terminal Strip Assortment, 1 box

#### Leadwire:

134-AWP, 100 ft (30 m)

126-DWV: Red, White, Black, Green, one 100-ft (30-m) roll each

326-DFV, 100 ft (30 m)

130-FWT: Red, White, Black, Green, one 50-ft (15-m) roll each

## **Protective Coatings:**

M-Coat A, two 1-oz (30-ml) bottles M-Coat B, two 1-oz (30-ml) bottles M-Coat C, 1-oz (30-ml) bottle M-Coat D, 1-oz (30-ml) bottle

M-Coat F, 1 kit

3145 RTV Silicone Rubber, 3-oz (85-g) tub

Mylar and Teflon are Registered Trademarks of DuPont.

Reference: An adhesive selection table is provided in the "M-Bond Strain Gage Adhesives."



# **Legal Disclaimer Notice**

Vishay Precision Group, Inc.

# **Disclaimer**

ALL PRODUCTS. PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.

Document No.: 63999 Revision: 15-Jul-2014