

Signal Conditioning Amplifier System

FEATURES

- Accepts quarter, half, or full bridge; all bridge-completion gages built in, including 120/1000 and 350 Ω dummies
- Fully adjustable and regulated bridge excitation on each channel; up to 12 VDC by front-panel control
- Continuously variable amplifier gain up to 2100 by front-panel control
- · Separate bridge power switch
- Output 10 VDC at 100 mA, short-circuit-proof and current limiting standard
- LED null indicators provided on each channel to indicate amplifier and bridge-balance condition
- · High stability with temperature and time
- Frequency response up to 50 kHz

DESCRIPTION

The demands of today's measurement applications are more exacting than ever before. An instrumentation system must provide durability and versatility, reliability with ease of operation, and economy with no sacrifice of accuracy.

The 2100 System was engineered with all of these requirements in mind, and to provide a durable, multi-channel signal conditioner/amplifier system capable of performing equally well in a wide variety of test applications and environments, and the 2100 System has proven itself through applications ranging from measurements on the ocean floor to testing of rocket motors.

The 2100 System accepts low-level signals, and conditions and amplifies them into high-level outputs suitable for multiple-channel simultaneous dynamic recording. The 2100 System is compatible with all types of external data recorders requiring voltage-level inputs.

Strain gage, load/pressure transducer and nickel temperature sensor inputs can be handled by the 2100 System without any rewiring.

All operational controls are located on the front panel for maximum setup efficiency. Frequently used controls are finger-operated, while initial setup adjustments are made through the front panel with a screwdriver.

Continuously variable amplifier gain is achieved via a locking ten-turn concentric-dial counting knob, which permits resetting to a predetermined value for repeating routine tests.

ADDITIONAL DETAILS

A separate bridge power switch removes bridge excitation, enabling the operator to detect unwanted signals due to electrical interference and/or noise, thermocouple effects, and shifts of the instrument zero



during a long-term test. This feature is an absolute must for dynamic testing, and for validating test results.

An adjustable bridge excitation control on each channel permits excitation to be set as specified by the strain gage or transducer manufacturer. It also allows for any special consideration which may be dictated by the test material; for example, the poor thermal conductivity normally associated with plastics.

In addition to adjustable bridge excitation, each channel has its own regulator circuit. This prevents interaction of adjacent channels during setup or operation.

Each channel has a continuously variable gain control. In combination with recommended excitation, the independent gain control can provide a large output signal so that small signals can be resolved without overpowering the strain gage or transducer.

An LED display for each channel gives positive indication of amplifier and resistive balance. This capability accelerates setup and verifies tension/ compression loading.

Easily read reference marks on the setup meter indicate acceptable line voltage and proper operation of internal power supplies.

A switch contained in the Model 2110B Power Supply allows adjustment when the line voltage is too high or too low.

The 2100 System provides true quarter bridge, threeleadwire capability, including internal dummies and sufficient plug connections for remote shunt calibration.

A convenient network in the Model 2120B Strain Gage Conditioner/Amplifier allows the operator to change the factory-supplied shunt values, as well as shunt any arm of the bridge, as required.



Signal Conditioning Amplifier System

MODEL 2120B STRAIN GAGE CONDITIONER AMPLIFIER

A two-channel plug-in amplifier module that includes bridge completion, bridge balance, amplifier balance, bridge excitation regulator, and shunt calibration.



> LED DISPLAY Setup/Indicator for amplifier balance, bridge balance, (tension/compression

BRIDGE BALANCE Resistively balances the bridge; standard locking knob; digital locking knob ("K" option)

GAIN RANGE AND VERNIER Varies amplifier gain between 1–2100

BRIDGE EXCITATION Varies bridge excitation between 0.5–12 VDC

AMPLIFIER BALANCE Adjusts amplifier offset

SHUNT CALIBRATION (2 points)

BRIDGE EXCITATION (on/off) Removes bridge excitation



Rear Panel



SPECIFICATIONS

All specifications are nominal or typical at +73°F (+23°C) unless noted.

PARAMETER	SPECIFICATIONS	
INPUT BRIDGE TYPE	 Quarter (120/1000 Ω and 350 Ω) Half and full bridge (50–1000 Ω) Quarter-bridge dummy gages provided 	
BRIDGE EXCITATION		
Voltage:	0.5 to 12 VDC (adjustable for each channel) with 120 Ω full-bridge load.	
Short-circuit current: Under ripple, noise, and 10%	<40 mA	
line change:	±2 mV max	
Load regulation:	$\pm 0.2\%$ no-load to 120 Ω load (10% line change)	
BRIDGE BALANCE	±2000 με (quarter, half, or 350 Ω full bridge). Range can be changed by internal jumper to ±4000 με or ±6000 με	



Signal Conditioning Amplifier System

PARAMETER	SPECIFICATIONS		
SHUNT CALIBRATION	Two-position (center off) toggle switch Standard factory-installed resistors ($\pm 0.1\%$) simulate $\pm 1000 \ \mu\epsilon$ at GF=2		
AMPLIFIER GAIN	1 to 2100 continuously adjustable ±1%		
BANDPASS			
Normal:	DC to 5 kHz (min): -0.5 dB (-5%) DC to 15 kHz: -3 dB		
Extended (using internal jumper):	DC to 17 kHz: -0.5 dB DC to 50 kHz: -3 dB		
AMPLIFIER INPUT			
Temperature coefficient of zero:	±1 μV/°C RTI* ±210 μV/°C RTO** (-10°C to +60°C, after 30 minute warm-up) *Referred to input **Referred to output		
Noise RTI (350 Ω source impedance):	 1 μVp-p at 0.1 Hz to 10 Hz 2 μVRMS at 0.1 Hz to 50 kHz 		
Noise RTO:	 50 μV p-p at 0.1 Hz to 10 Hz 80 μV p-p at 0.1 Hz to 100 Hz 100 μVRMS at 0.1Hz to 15 kHz 200 μVRMS at 0.1Hz to 50 kHz 		
Input Impedance:	$>$ 100 M Ω (balance limit resistor disconnected)		
Common-Mode Rejection (DC to 60 Hz):	Gain Multiplier	CMR (dB)	
	x2	67	
	X20	87	
	x200	100	
Source Current:	±10 nA typical; ±40 nA max.	±10 nA typical; ±40 nA max.	
OUTPUT	±10 V (min) at ±100 mA		
Current limit:	140 mA		
SIZE	5.25 H x 2.94 W x 10.97 D in (133 x 75 x 279 mm)		
WEIGHT	2.2 lb (1.0 kg)		



2100 System

Signal Conditioning Amplifier System

MODEL 2110B - POWER SUPPLY

A plug-in module capable of powering up to ten channels (five Model 2120B modules) at a maximum rated voltage or current. Provides initial bridge and amplifier voltages. All supplies are current-limited against amplifier malfunction.



BRIDGE-VOLTS METER Vsed to set up/monitor bridge excitation, also line and power supply levels

CHANNEL SELECTOR AC monitors ac line input. DC monitors the power supplies. Positions 1–10 select and display bridge excitation for each channel

PILOT LAMP Indicates main power

POWER SWITCH Main power on-off

EXTERNAL METER Used with an external digital voltmeter to precisely adjust bridge excitation

SPECIFICATIONS

All specifications are nominal or typical at +73°F (+23°C) unless noted.

PARAMETER	SPECIFICATIONS	
INPUT VOLTAGE	107, 115, 214, 230 VAC ±10% 50/60 Hz (selected internally)	
Power:	40 W typical, 100 W max.	
OUTPUTS VOLTAGES	 ±15 V at 1.2 A +17.5 V at 1.1 A; All regulators current-limited against overload 	
METER	 0 to 12 VDC (with switch) to read bridge excitation. AC input and DC output go/no-go monitor 	
SIZE	5.25 H x 2.44 W x 12.34 D in (133 x 62 x 313 mm)	
WEIGHT	6.7 lb (3.1 kg)	

2100 System

A prewired rack adapter which accepts one Model 2110B and up to five Model 2120B Strain Gage Conditioner Amplifiers. It has its own fuse and power cord and can be housed in any standard 19-in (483-mm) electronic equipment rack.



MODEL 2150 - RACK ADAPTER

MODEL 2150 FRONT



ICROE **TEASUREMENTS** A VPG Brand

PARAMETER	SPECIFICATIONS
POWER CABLE	2-ft (0.6-m) 3-wire line cord; 10-ft (3-m) extension available Receptacle to accept line cord from adjacent 2150 Rack Adapter
SIZE	5.25 H x 19 W x 14.17 D in (133 x 483 x 360 mm)
WEIGHT	6.6 lb (3.0 kg)

Signal Conditioning Amplifier System

MODEL 2160B PORTABLE FOUR-CHANNEL ENCLOSURE

A prewired, fused enclosure which houses up to three (3) modules. A carrying handle ensures maximum portability. An additional snap-down bail support on the bottom can be used to elevate the 2160 for excellent work efficiency during bench-top operation. The Model 2160 would be substituted for the Model 2150 when two or four channels and maximum portability are required.



PARAMETER	SPECIFICATIONS
SIZE	5.55 H x 8.75 W x 13.80 D in (141 x 222 x 350 mm)
WEIGHT	5.2 lb (2.4 kg)



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.